

# Product data sheet

## Characteristics

# GU7590BBC

Ultimate Low profile - shaver socket - chrome/  
black



## Main

Range of product	Ultimate
Aesthetic name	Low profile
Product or component type	Shaver socket
Input voltage	230 V AC 50 Hz
Colour tint	Chrome brushed finish Black

## Complementary

Material	Metal
Fixing mode	By screws M3.5 x 30 mm
Device mounting	Flush
Connections - terminals	Screw terminals
Quantity per set	Set of 1
Height	148 Mm
Width	88 Mm
Depth	47 Mm
Surface treatment	Untreated
Surface finish	Matt

## Environment

Standards	BS EN 61558-2-5
IP degree of protection	IP20

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**