



Main

Range of product	Ultimate
Range	Ultimate
Aesthetic name	Grid system
Product or component type	Switch module
Control type	Toggle switch
Switch function	2-way
Rated current	16 AX at 230 V AC

Complementary

Connections - terminals	Screw terminals
Material	Steel Urea (carbamide) PC (polycarbonate)
Quantity per set	Set of 1
Number of modules	1 module
Device mounting	Wall mounted
Height	59 Mm
Width	25 Mm
Depth	36 Mm

Environment

Standards	BS EN 60669-1
IP degree of protection	IP20

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.