

Product data sheet

Characteristics

H361CLR

SW FUSIBLE HD 30A 3P NEMA1/CLASS R KITS



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 750.00 USD

Main

Disconnecter device type	Fusible disconnect switch
Enclosure type	Enclosure standard environment indoor
Series name	Heavy duty

Complementary

Rated current	30 A
AWG gauge	AWG 14...AWG 6 copper AWG 12...AWG 6 aluminium
Device mounting	Surface
Electrical connection	Receptacle Crouse-Hinds Arktite Lugs
Enclosure material	Steel
Interlocking type	Without electrical interlock
Number of poles	3
Permissible voltage	<= 600 V
Short-circuit protection	200 kA R or J 10 kA H or K
Switch function	TPST
Wiring configuration	Without neutral

Environment

NEMA degree of protection	NEMA 1
Product certifications	UL listed

Ordering and shipping details

Category	00160 - DE1 MISC
Discount Schedule	DE1
GTIN	00785901694137
Nbr. of units in pkg.	1
Package weight(Lbs)	9
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : Commercialised