

Product data sheet

Characteristics

HJL36030M71AA

Motor circuit protector, PowerPact H, 30A, 3 pole, 600V, 25kA, auxiliary switch



by Schneider Electric

Price*: 1386.00 USD



Main

Product or component type	Motor Circuit Protector
Range of product	PowerPact H
Trip unit technology	Electronic
Breaking capacity code	J
Accessory / separate part type	Auxiliary switch 1 NC + 1 NC

Complementary

Line Rated Current	30 A
Poles description	3P
Breaking capacity	100 KA 240 V AC 65 KA 480 V AC 25 KA 600 V AC
[Ue] rated operational voltage	600 V AC
Continuous current rating	80 %
Mounting mode	Unit mount
Electrical connection	Lugs load Lugs line
AWG gauge	AWG 14...AWG 3/0 aluminium/copper
[Ith] conventional free air thermal current	1.5...25 A
Magnetic tripping current	9...325 A
Maximum Height	6.4 In (162.56 mm)
Width	4.12 In (104.65 mm)
Depth	4.36 In (110.74 mm)
Tightening torque	44.25 Lbf.In (5 N.m) 0.00...0.15 in ² (2.5...95 mm ²) AWG 14...AWG 3/0

Environment

Product certifications	UR IEC CE
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	01125-HJ, JJ UNT MNT MTR CIRCUIT PROTECTR
Discount Schedule	DE2
GTIN	00785901553342
Package weight(Lbs)	5.00 Lb(US) (2.268 kg)
Returnability	No
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**