

# Product data sheet

## Characteristics

# HMIYPMAC61

## Module AC power supply for Panel PC 12"

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 225.00 USD



### Commercial status

This Product is Obsolete :

 This Product is Obsolete

### Main

Range of product	Magelis iPC
Product or component type	Power supply
Accessory / separate part category	Spare part

### Complementary

Product weight	1.32 lb(US) (0.6 kg)
Accessory / separate part destination	Magelis Panel PC 12" for 1 port
Input voltage	100...240 V AC at 45...65 Hz
Input current	20 mA at 100 V AC
Output voltage	24 V DC +/- 10 %
Line Rated Current	5.5 A
Range compatibility	Magelis iPC

### Environment

Ambient air temperature for operation	32...131 °F (0...55 °C)
Ambient air temperature for storage	-4...140 °F (-20...60 °C)
Relative humidity	5...90 % non-condensing
IP degree of protection	IP20 conforming to EN 60529
Vibration resistance	0.5 gn 9...150 Hz 1 gn 9...150 Hz 2 gn 8...200 Hz 4 gn 200...500 Hz 1.75 mm 2...9 Hz 3.5 mm 2...9 Hz 7.5 mm 2...9 Hz
Shock resistance	15 gn operation 11 ms 30 gn transport 6 ms 30 gn storage 6 ms

## Ordering and shipping details

Category	22575 - MAGELIS MC3
Discount Schedule	MC3
GTIN	003595864172835
Nbr. of units in pkg.	1
Package weight(Lbs)	0.9000000000000002
Returnability	N
Country of origin	AT

Product Life Status : **End of commercialisation**