

Product data sheet

Characteristics

HOM2024L125TCI

LOAD Center HOM RPLCMT INT ASSY 125



by Schneider Electric

Price*: 227.00 USD

Commercial status

This Product is Obsolete :

This Product is Obsolete

Main

Product or component type	Load Center Interior Assembly
Range of product	Homeline
Load center type	Main lugs
Line Rated Current	125 A
Number of spaces	20
Short-circuit current	10 kA
Number of circuits	24
Number of tandem circuit breakers	4
Phase	1 phase
System Voltage	120/240 V AC

Complementary

AWG gauge	AWG 6...AWG 2/0 (copper)
Device composition	Grounding bar (factory installed)
Wiring configuration	3-wire
Material	Tin plated aluminium busbar
Product certifications	UL listed file E-6294

Ordering and shipping details

Category	00185 - MISC. HOM LOAD CENTERS
Discount Schedule	DE3C
Nbr. of units in pkg.	1
Package weight(Lbs)	10
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	Lifetime
-----------------	----------

Product Life Status : **End of commercialisation**