

Product data sheet

Characteristics

HOM20M100CI

Homeline, LC interior, 100 A, 120/240 V, 1 PH, MB, 20 SP, grd bar



by Schneider Electric

Price*: 308.00 USD



Main

Product or component type	Load Center Interior Assembly
Range of product	Homeline
Load center type	Main breaker
Line Rated Current	100 A
Number of spaces	20
Short-circuit current	22 KA
Number of circuits	20
Number of tandem circuit breakers	0
Phase	1 phase
[Ue] rated operational voltage	120/240 V AC

Complementary

AWG gauge	AWG 6...AWG 1 aluminium AWG 6...AWG 1 copper
Device composition	Grounding bar (ordered separately)
Wiring configuration	3-wire
Material	Tin plated aluminium busbar

Environment

Ambient air temperature for operation	23 °F (-5 °C) 104 °F (40 °C)
Product certifications	UL listed file E-6294

Ordering and shipping details

Category	00185-MISC. HOM LOAD CENTERS
Discount Schedule	DE3C
Package weight(Lbs)	10.00 Lb(US) (4.536 kg)
Returnability	No

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive-harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Will be compliant – Date to be confirmed

Contractual warranty

Warranty	Lifetime
----------	----------

Product Life Status : **Commercialised**