

Product data sheet

Characteristics

HOM612L100F

LOAD Center HOM MLO 240V 100A 1PH 6SP



by Schneider Electric

Product availability: Stock - Normally stocked in distribution facility

Price*: 78.00 USD



Main

Product or component type	Load Center
Range of product	Homeline
Load center type	Main lugs
Line Rated Current	100 A
Number of spaces	6
Number of circuits	12
NEMA degree of protection	NEMA 1 indoor
Cover type	Flush cover
Electrical connection	Lugs

Complementary

Short-circuit current	10 kA
Number of tandem circuit breakers	6
Phase	1 phase
System Voltage	120/240 V AC
AWG gauge	AWG 8...AWG 1 (aluminium/copper)
Wiring configuration	3-wire
Cover finish	Gray baked enamel
Material	Tin plated aluminium busbar
Enclosure material	Welded sheet steel
Surface finish	Baked enamel grey
Box number	4
Height	319 mm
Width	8.9 in (226 mm)
Depth	4.25 in (108 mm)

Environment

Product certifications	UL E-6294
------------------------	-----------

Ordering and shipping details

Category	00149 - HOM 2-8 CKT,MLO,NEMA1&3R
Discount Schedule	DE3C
GTIN	00785901061182
Nbr. of units in pkg.	1
Package weight(Lbs)	7.96
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1248 - Schneider Electric declaration of conformity Schneider-Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	Lifetime
-----------------	----------

Product Life Status : **Commercialised**