

Product data sheet

Characteristics

HOMT225250CP

Miniature Breaker - Homeline - Quad - CP -
120/240V - 10kA - 25/50A - UL Listed



Product availability: Stock - Normally stocked in distribution facility



Main

Product or component type	Miniature circuit-breaker
Range of product	Homeline
Line Rated Current	25 A 50 A
Product certifications	UL listed
System Voltage	120/240 V AC
Poles description	2P
Short-circuit current	10 kA
Number of spaces required	2
Circuit breaker type	Quad tandem
Circuit breaker application	HACR rated
Electrical connection	Box lugs
AWG gauge	AWG 14...AWG 8 for 1 cable(s) (aluminium/copper) AWG 14...AWG 6 for 1 cable(s) (aluminium/copper)
Type of packing	Consumer packaging
Height	3.13 in
Width	1.97 in
Depth	3.29 in

Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	01335 - HOMELINE QUAD BRKRS.
Discount Schedule	CPH
GTIN	00785901961420
Nbr. of units in pkg.	5
Package weight(Lbs)	1

Returnability	Y
Country of origin	MX

Contractual warranty

Warranty period	Miniature Breaker - Homeline - Quad - CP - 120/240V - 10kA - 25/50A - UL Listed
-----------------	---

Product Life Status : **Commercialised**