

Product data sheet

Characteristics

HOMVP12

LOAD Center 150AMP QO+HOM +OPTIONS



by Schneider Electric

Price*: 983.00 USD



Commercial status

This Product is Obsolete :

This Product is Obsolete

Main

Cover type	Combination flush/surface cover
Device application	Value pack
Provided equipment	5 HOM120 circuit breaker 1 HOM230 circuit breaker 1 HOM30M150C circuit breaker
Range of product	Homeline

Complementary

AWG gauge	AWG 4...250 kcmil aluminium/copper
Box number	10R
Depth	3.75 In (95.25 mm)
Device composition	Grounding bar (ordered separately)
Maximum Height	33.78 In (858.01 mm)
Load center type	Main breaker
Number of spaces	30
Short-circuit protection	22 KA
Width	14.25 In (361.95 mm)
Wiring configuration	3-wire

Environment

Product certifications	UL Listed
------------------------	-----------

Ordering and shipping details

Category	00185-MISC. HOM LOAD CENTERS
Discount Schedule	DE3C
GTIN	00785901401711
Package weight(Lbs)	34.23 Lb(US) (15.526 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commercialisation**