

# HVL415DEGR2

HVL Single Digest Switch 15KV NEMA 1 DIN/E  
Current Limit Fuse 125-200E XFMR RH



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 20614.00 USD

## Main

Product or component type	Transformer Disconnect
Provided equipment	Fuse to be ordered separately
Device application	Transformer connection: right side

## Complementary

Protection type	Fuse current limiter
Associated fuse rating	125 A E 150 A E 175 A E 200 A E
Line Rated Current	600 A
Braking current	40 kA
Load current	300 A
Network frequency	50/60 Hz
Poles description	3P
[Ur] highest voltage for equipment	15 kV
[Ui] rated insulation voltage	95 kV
NEMA degree of protection	NEMA 1
Electrical connection	Lugs
AWG gauge	AWG 2...600 kcmil aluminium/copper
Enclosure nominal width	38 in
Enclosure nominal depth	54.5 in
Enclosure nominal height	90 in

## Environment

Product certifications	UL listed CUL
------------------------	------------------

Ordering and shipping details

Category	07944 - 15KV DIGEST HVL NEMA 1
Discount Schedule	PE5A
Nbr. of units in pkg.	1
Package weight(Lbs)	1200
Returnability	N
Country of origin	US

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : Commercialised