

# HVL505DEWRH

HVL Duplex Digest Switch 5KV NEMA 3R DIN/E  
Current Limit 10-450E XFMR RH



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 49484.00 USD

## Main

Product or component type	Transformer Disconnect
Provided equipment	Fuse to be ordered separately
Device application	Transformer connection: right side

## Complementary

Protection type	Fuse current limiter
Associated fuse rating	10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E 125 A E 150 A E 175 A E 200 A E 250 A E 300 A E 400 A E 350 A E 500 A E
Line Rated Current	600 A
Braking current	40 kA
Load current	300 A
Network frequency	50/60 Hz
Poles description	3P
[Ur] highest voltage for equipment	4.76 kV
[Ui] rated insulation voltage	60 kV
NEMA degree of protection	NEMA 3R

Electrical connection	Lugs
AWG gauge	AWG 2...600 kcmil aluminium/copper
Enclosure nominal width	76 in
Enclosure nominal depth	60 in
Enclosure nominal height	97 in

### Environment

Product certifications	CUL UL listed
------------------------	------------------

### Ordering and shipping details

Category	07943 - 5KV DIGEST HVL NEMA 3R
Discount Schedule	PE5A
Nbr. of units in pkg.	1
Package weight(Lbs)	2800
Returnability	N

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**