

HVL515DEGR1

HVL Duplex Digest Switch 15KV NEMA 1 DIN/E
Current Limit 10-100E XFMR RH



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 43084.00 USD

Main

Product or component type	Transformer Disconnect
Provided equipment	Fuse to be ordered separately
Device application	Transformer connection: right side

Complementary

Protection type	Fuse current limiter
Associated fuse rating	10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E
Line Rated Current	600 A
Braking current	40 kA
Load current	300 A
Network frequency	50/60 Hz
Poles description	3P
[Ur] highest voltage for equipment	15 kV
[Ui] rated insulation voltage	95 kV
NEMA degree of protection	NEMA 1
Electrical connection	Lugs
AWG gauge	AWG 2...600 kcmil aluminium/copper
Enclosure nominal width	76 in
Enclosure nominal depth	54.5 in
Enclosure nominal height	90 in

Environment

Product certifications	CUL UL listed
------------------------	------------------

Ordering and shipping details

Category	07944 - 15KV DIGEST HVL NEMA 1
Discount Schedule	PE5A
Nbr. of units in pkg.	1
Package weight(Lbs)	2800
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**