

Product data sheet

Characteristics

HVLCCA14315N

HVLcc Switch Unfused 15KV, 600A, 14.75IN

Application A



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 19244.00 USD

Main

Product or component type	Switch mechanism
Hub type	A

Complementary

Line Rated Current	600 A
Braking current	40 kA
Network frequency	50/60 Hz
Poles description	3P
[Ur] highest voltage for equipment	15 kV
[Ui] rated insulation voltage	95 kV
NEMA degree of protection	NEMA 1
Electrical connection	Lugs
AWG gauge	AWG 2...350 kcmil for 2 cable(s) aluminium/copper
Service feed location	OH
Enclosure nominal width	14.75 in
Enclosure nominal depth	37.25 in
Enclosure nominal height	90 in

Ordering and shipping details

Category	07948 - DIGEST HVL/CC
Discount Schedule	PE5A
Nbr. of units in pkg.	1
Package weight(Lbs)	445
Returnability	N
Country of origin	US

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : Commercialised