

HVLCCA14515DGR

HVLCC Duplex Switch 15KV,14.75IN Application A DRY XFMR RT



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 57428.00 USD

Main

| | |
|---------------------------|------------------------------------|
| Product or component type | Switched fuse mechanism |
| Hub type | A |
| Provided equipment | Fuse to be ordered separately |
| Device application | Transformer connection: right side |

Complementary

| | |
|------------------------------------|---|
| Protection type | Fuse current limiter |
| Associated fuse rating | 10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E 125 A E 150 A E 175 A E 200 A E |
| Line Rated Current | 600 A |
| Braking current | 40 kA |
| Load current | 300 A |
| Network frequency | 50/60 Hz |
| Poles description | 3P |
| [Ur] highest voltage for equipment | 15 kV |
| [Ui] rated insulation voltage | 95 kV |
| NEMA degree of protection | NEMA 1 |
| Electrical connection | Lugs |
| AWG gauge | AWG 2...350 kcmil for 2 cable(s) aluminium/copper |

| | |
|--------------------------|----------|
| Service feed location | OH |
| Enclosure nominal width | 29.5 in |
| Enclosure nominal depth | 37.25 in |
| Enclosure nominal height | 90 in |

Ordering and shipping details

| | |
|-----------------------|-----------------------|
| Category | 07948 - DIGEST HVL/CC |
| Discount Schedule | PE5A |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 925 |
| Returnability | N |
| Country of origin | US |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Product Life Status : **Commercialised**