



Main

Range	Thorsman
Product or component type	Digital multimeter
Supply	Battery 9 V

Complementary

Display type	Backlit monochrome STN LCD
Type of setting	Manual
Signalling function	Low battery by visual
Function available	Live AC wire detection Stand alone equipment control Data hold function Non-contact AC voltage detection
Protection type	Fuse
Type of measurement	Resistance: 200 Ohm/2/20/200 kOhm/20 MOhm Battery voltage: 1.5/9 V/12 V Continuity: < 100 Ohm Voltage DC: 0.2/2/20/200/300 V Voltage AC: 0.2/2/20/200/300 V Current DC: 20 mA/200 mA/10 A Temperature: 0...1000 °C
Measurement category	Category III 300 V
Language	Swedish Finnish Danish Norwegian English
Height	165 Mm
Width	85 Mm
Depth	39 Mm
Net weight	290 G with battery

Environment

Standards	IEC 61010
-----------	-----------

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
China RoHS Regulation	China RoHS Declaration

Product Life Status : **Commercialised**