



Main

Product or component type	Socket-outlet tester
Outlet standard	British

Complementary

Local signalling	Ground error by LCD display
Function available	RCD test function
Rated voltage	220 V 50...60 Hz +/- 10 %
Measurement category	Category III 300 V
Residual current	30 MA +/- 15 %
Response time	60...300 ms
Threshold tripping voltage	< 35 V AC
Height	77 Mm
Width	67 Mm
Depth	66 Mm
Net weight	70 G

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation

Product Life Status : **Commercialised**