

Main

Range	Thorsman
Product or component type	Voltage tester

Complementary

Local signalling	LED if presence of voltage Sound indicator alarm if presence of voltage
Measurement voltage	5...1000 V AC
Network frequency	50...400 Hz
Measurement category	Category IV 1000 V
Language	Finnish Danish Swedish English Norwegian
Height	152 mm
Width	32 mm
Depth	28 mm

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.