



Main

Range	Thorsman
Product or component type	Test meter
Supply	2 battery 3 V

Complementary

Display digits	3.5
Type of setting	Automatic reset
Signalling function	Low battery by visual
Function available	High precision measuring Audible continuity Tactile barrier for safety Data hold function
Type of measurement	Voltage DC: 200mV/2/20/200/600 V Resistance: 200 Ohm/2/20/200 kOhm/20 MOhm Voltage AC: 2/20/200/600 V Current AC: 2/20/200/600 A Continuity: < 30 Ohm Diode check: 1.5 V
Measurement category	Category III 600 V
Language	Finnish Swedish Danish Norwegian English
Height	190 Mm
Width	76 Mm
Depth	36 Mm
Net weight	160 G with battery

Environment

Standards	IEC 61010
-----------	-----------

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
China RoHS Regulation	China RoHS Declaration

Product Life Status : **Commercialised**