



Main

Range	Thorsman
Product or component type	Digital multimeter
Supply	Battery 9 V


Complementary

Display type	Backlit monochrome STN LCD
Type of setting	Manual
Signalling function	Low battery by visual
Function available	Stand alone equipment control Non-contact AC voltage detection Data hold function Live AC wire detection
Protection type	Fuse
Type of measurement	Resistance: 200 Ohm/2/20/200 kOhm/20 MOhm Battery voltage: 1.5/9 V/12 V Continuity: < 100 Ohm Voltage DC: 0.2/2/20/200/300 V Voltage AC: 0.2/2/20/200/300 V Current DC: 20 mA/200 mA/10 A Temperature: 0...1000 °C
Measurement category	Category III 300 V
Language	German Spanish French Polish Portuguese
Height	165 Mm
Width	85 Mm
Depth	39 Mm
Net weight	290 G with battery

Environment

Standards	IEC 61010
-----------	-----------

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation

Product Life Status : **Commercialised**