



Main

Range	Thorsman
Product or component type	Digital multimeter
Supply	Battery 12 V

Complementary

Type of setting	Manual
Signalling function	Low battery by visual
Function available	Handsfree operations
Protection type	Fuse
Type of measurement	Current DC: 200 mA Voltage AC/DC: 2/20/200/300 V Resistance: 2/20/200 kOhm/2 MOhm
Measurement category	Category III 300 V
Language	German Polish French Spanish Portuguese
Height	120 Mm
Width	75 Mm
Depth	18 Mm
Net weight	110 G with battery

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
China RoHS Regulation	China RoHS Declaration

Product Life Status : **Commercialised**