



Main

Range	Thorsman
Product or component type	Analog multimeter
Supply	Battery 1.5 V

Complementary

Type of setting	Manual
Function available	Handsfree operations
Protection type	Fuse
Type of measurement	Resistance: x10 Ohm/x1 kOhm Voltage DC: 12/60/120/300 V Voltage AC: 12/60/300 V Current DC: 0.6/12/600 mA
Measurement category	Category III 300 V
Relative humidity	0...85 %
Language	French Polish Hungarian
Height	140 Mm
Width	75 Mm
Depth	50 Mm
Net weight	275 G without battery

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation

Product Life Status : **Commercialised**