



Commercial status

End of Commercialisation :

 End of Commercialisation

Main

Range	Thorsman
Product name	Goliath 38
Product or component type	Work lamp
Light source	Compact fluorescent tube 38 W

Complementary

Type of installation	Outdoor Indoor
[Ue] rated operational voltage	230 V
Plug pole configuration	2P
Plug standard	European
Luminous flux	2850 Lm
Bulb lifespan	8000 H
Colour rendering index	R _A =82
Illuminance	3 m: 134 lux 1 m: 1210 lux
Cable insulation material	Neoprene
Housing material	PC + rubber
Electrical connection	Feed power cord H07RN-F2x1.0 5 m
Electrical insulation class	Class II
Marking	F ENEC 15
Height	280 Mm
Width	280 Mm
Depth	90 Mm
Net weight	2.7 Kg

Environment

IP degree of protection	IP54
Quality labels	CE ENEC
Ambient air temperature for operation	-15...50 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Product Life Status : **End of commerc. - Block**