



Main

Range	Mureva
Product or component type	Junction box
Colour tint	White (RAL 9010)
Quantity per set	Set of 1

Complementary

Device mounting	Surface
Fixing mode	By screws : cover
Base dimension	82 x 82 x 55 mm
Cable entry	Grommets
Cable entry number	6 x 19 mm
Material	ABS (acrylonitrile butadiene-styrene) : body and cover SEBS (styrene ethylene butylene styrene) : grommet
Connections - terminals	Without terminal
Height	82 mm
Width	82 mm
Depth	55 mm

Environment

Ambient air temperature for operation	-25...40 °C
IP degree of protection	IP44
Fire resistance	650 °C
Standards	EN 60670
Product certifications	CE
Environmental characteristic	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1838 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	----------------