



Main

Range	Mureva
Product or component type	Rigid conduit
Shape	Tuliped ends
Function available	GT-function
Mounting location	Outdoor Indoor
Nominal cross section	133 mm ²
Diameter	External : 16 mm Internal : 13 mm
Colour tint	Grey (RAL 7035)
Length	2 m

Complementary

Pulling force	750 N
Material	PVC (polyvinyl chloride)
Quantity per set	50 m
Ambient air temperature for operation	-5...60 °C
Standards	IEC 61386

Environment

IK degree of protection	IK07
Product certifications	NF
Environmental characteristic	Non-flame propagating
Environmental health and issues	Lead free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1839 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	----------------