Product data sheet
Characteristics

IMT43340
Mureva Tube GT - GT bend - diam. 40 - grey - IP40

Commercial status
End of Commercialisation : APR 28, 2022

⚠ End of Commercialisation

Main

Range	Mureva
Product or component type	Bend
Function available	GT-function
Mounting location	Outdoor Indoor
Nominal cross section	984 Mm²
Diameter	External: 40 mm Internal: 35.4 mm
Colour tint	Grey (RAL 7035)

Complementary

Quantity per set	1 piece
Ambient air temperature for operation	-5…60 °C
Material	PVC (polyvinyl chloride)
Standards	IEC 61386

Environment

IP degree of protection	IP40
IK degree of protection	IK07
Environmental characteristic	Non-flame propagating
Product certifications	NF

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 Cm
Package 1 Width	4.5 Cm
Package 1 Length	42 Cm
Package 1 Weight	144 G

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months

Product Life Status : End of commerc. - Block

IMT43340 may be replaced by any of the following products:

IMT53340

GT bend, Mureva Tube GT, diameter 40mm, IP40, grey

Qty 1

Substitution date: |