



Main

Range	Mureva
Product name	Mureva Tube GT
Product or component type	Bend
Device application	Bend and tee joining
Function available	GT-function
Mounting location	Outdoor Indoor
Diameter	External : 16 mm Internal : 13 mm
Colour tint	White (RAL 9003)

Complementary

Quantity per set	100 pieces
Ambient air temperature for operation	-5...60 °C
Material	PVC (polyvinyl chloride)
Standards	IEC 61386

Environment

IP degree of protection	IP40
IK degree of protection	IK07
Environmental characteristic	Non-flame propagating
Product certifications	NF

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2019
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.