



Main

Range	Mureva
Product or component type	Rigid conduit
Shape	Tuliped ends
Function available	GT-function
Mounting location	Indoor Outdoor
Nominal cross section	907 mm ²
Diameter	Internal : 34 mm External : 40 mm
Colour tint	Black (RAL 9005)
Length	3 m

Complementary

Pulling force	750 N
Material	PP (polypropylene)
Quantity per set	21 m
Ambient air temperature for operation	-25...105 °C
Standards	IEC 60754-2 IEC 60754-1 IEC 61386 EN 50267-2-2 EN 50267-2-1

Environment

IP degree of protection	IP30
IK degree of protection	IK07
Product certifications	NF
Environmental characteristic	Non-flame propagating
Environmental health and issues	LSF (Low Smoke and Flame Retardance) Halogen free

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1839 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	----------------