



Main

Range	Mureva
Product or component type	Bend
Mounting location	Outdoor Indoor
Nominal cross section	907 mm ²
Diameter	Internal : 34 mm External : 40 mm
Colour tint	Black (RAL 9005)


Complementary

Quantity per set	35 pieces
Ambient air temperature for operation	-25...95 °C
Material	PC/ABS
Standards	IEC 61386

Environment

IP degree of protection	IP30
IK degree of protection	IK07
Environmental characteristic	Non-flame propagating
Environmental health and issues	Halogen free

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1201 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**