



Main

Range of product	Stago
Product or component type	Bend
Provided equipment	1 cover
Colour tint	White RAL 1013
Quantity per set	Set of 1

Complementary

Trunking dimension	170A x 65 mm
Compartment partitioning	1 compartment
Operating angle	90 °
Direction change type	Vertical
Front opening size	80 mm
Nominal cross section	11050 mm ²
Fixing mode	By brackets By screws
Material	Zinc coated sheet steel
Surface finish	Powder coated
Length	250 mm
Height	170 mm
Width	65 mm
Compatibility code	WGX-LSN170A

Environment

Standards	EN 50085-1 : 2005 EN 50085-2-1 : 2006
Directives	73/23/EEC - low voltage directive
Ambient air temperature for operation	-20...80 °C
Environmental health and issues	Halogen free
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1826 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**