



### Main

Range of product	Stago
Product or component type	Bend
Provided equipment	1 cover
Colour tint	Optional
Quantity per set	Set of 1

### Complementary

Trunking dimension	165W x 52 mm
Compartment partitioning	1 compartment
Operating angle	90 °
Direction change type	Vertical
Front opening size	80 mm
Nominal cross section	8580 mm <sup>2</sup>
Fixing mode	By brackets By screws
Material	Zinc coated sheet steel
Surface finish	Powder coated
Length	250 mm
Height	165 mm
Width	52 mm

### Environment

Standards	EN 50085-1 : 2005 EN 50085-2-1 : 2006
Directives	73/23/EEC - low voltage directive
Ambient air temperature for operation	-20...60 °C
Environmental health and issues	Halogen free
IP degree of protection	IP20

Product Life Status : **Commercialised**