



Main

Range of product	Optiline
Cabling installation system	Trunking
Product or component type	Mini trunking
Product compatibility	Mini trunking

Complementary

Trunking material	Plastic
Compartment partitioning	3 compartments
Colour tint	White (RAL 9010)
Trunking dimension	25 x 60 mm
Fixing mode	Pre-punched fixing hole 100 mm Power cable: screw-fixed
Material	PVC (polyvinyl chloride)
Quantity per set	21 m
Ambient air temperature for operation	-25...60 °C
Length	2100 Mm
Height	60 Mm
Width	25 Mm

Environment

Standards	73/23/EEC EN 50085-1:2005 EN 50085-2-1:2006
IP degree of protection	IP40
IK degree of protection	IK07

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------