Product data sheet
Characteristics

JD250S
Circuit breaker enclosure, PowerPacT J, 150A to 250A, NEMA 1, surface mount

Product availability: Stock - Normally stocked in distribution facility

Price*: 285.00 USD

Main

Circuit breaker type	JDL
Product destination	Circuit breaker J-Frame 3P

Complementary

Line Rated Current	150…250 A
Device mounting	Surface
Poles description	3P
Enclosure Material	Steel
Height	31.38 In (797 mm)
Width	14.37 In (365 mm)
Depth	5.98 In (152 mm)

Environment

Product Certifications	CSA[RETURN]UL

Environmental

NEMA degree of protection	NEMA 1

Ordering and shipping details

Category	US10DE100030
Discount Schedule	0DE1
GTIN	785901599241
Returnability	Yes
Country of origin	US

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.19 In (20.8 cm)
Package 1 Width	8.31 In (21.1 cm)
Package 1 Length	32.80 In (83.3 cm)
Package 1 Weight	17.15 Lb(US) (7.78 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months

Product Life Status : Commercialised