



Main

Range of product	Canalis
Product or component type	Feed unit
Material	Aluminium
Product compatibility	KBB
[Ie] rated operational current	25 A 40 A
Mounting location	Central
Colour	White (RAL 9003)

Complementary

Protection type	Without protection
[Ue] rated operational voltage	230...400 V
Connections - terminals	Terminal block - Pg 21 for 10 mm ²
Control type	Communicating
Number of circuits	1
Provided equipment	End cover
Mounting mode	By clips
Mounting support	Busbar
Standards	IEC 61439-6 IEC 60439-2
Width	244 Mm
Depth	75.5 Mm
Height	75.5 Mm

Environment

IP degree of protection	IP55 conforming to IEC 60529
-------------------------	------------------------------

Product Life Status : **Commercialised**