



Commercial status  
End of Commercialisation :

⚠ End of Commercialisation

### Main

Range	C-Bus
Product or component type	Dimmer
Device application	Control
Load type	Incandescent: 20 W (minimum)
Provided equipment	Miniature circuit breaker (MCB), 1 RCCB, 4
Number of channels	3

### Complementary

Maximum leakage current	10 mA leading edge
[Us] rated supply voltage	240 V AC 47...53 Hz 415 V AC 47...53 Hz
Starting time	0.5 s
Rated breaking capacity	6 KA
[Ui] rated insulation voltage	500 V

### Environment

Dielectric strength	2500 V
Directives	2002/95/EC - RoHS directive 2004/108/EC - electromagnetic compatibility
Standards	EN 61000-3-2 EN 61000-3-3 EN 55015 IEC 60669-2-1 AS/NZS CISPR 15 AS/NZS CISPR 14-1 IEC 60439-1 AS/NZS 3439-1 EN 61000-3-11 EN 55014-1 EN 61000-3-5

## Offer Sustainability

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope) [EU RoHS Declaration](#)

Product Life Status : **End of commercialisation**