

Product data sheet

Characteristics

LA26225BC

2P 225A, 600V, LA 4PHASE FA/LA MOLDED CASE CIRCUIT BREAKER



by Schneider Electric



Price*: 4053.00 USD

Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip unit technology	Thermal-magnetic
Breaking capacity code	A

Complementary

Line Rated Current	225 A
Poles description	2P
Breaking capacity	42 KA 120 V AC 42 KA 240 V AC 30 KA 480Y/277 V AC 30 KA 480 V AC 22 KA 600 V AC 10 KA 125 V DC 10 KA 250 V DC
[Ue] rated operational voltage	600 V AC 125 V DC 250 V DC
Mounting mode	I-Line
Electrical connection	Lugs load I-Line connection line
AWG gauge	AWG 1...600 kcmil aluminium/copper)1 AWG 1...250 kcmil aluminium/copper)2
Terminal identifier	AL400LA
Magnetic hold current	1125 A
Magnetic tripping current	2250 A
Wiring configuration	4-wire
Phase connection	BC
Maximum Height	11 ln (279.40 mm)
Maximum Width	6 ln (152.40 mm)
Maximum Depth	5.84 ln (148.34 mm)
Tightening torque	115.06 Lbf.In (13 N.m) 0.07...0.47 in ² (42...304 mm ²) AWG 1...600 kcmil 115.06 Lbf.In (13 N.m) 0.07...0.20 in ² (42...127 mm ²) AWG 1...250 kcmil

Environment

Product certifications	UL Listed CSA
------------------------	------------------

Ordering and shipping details

Category	01040-LA/LH BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901562832
Package weight(Lbs)	16.13 Lb(US) (7.315 kg)
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP and DIDP- which is known to the State of California to cause Carcinogen and Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**