

# LAP36250MB

## FA/LA MOLDED CASE CIRCUIT BREAKER, 600V, 250A, 3P, I-Line, SHORT HANDLE



by Schneider Electric

Product availability: Stock - Normally stocked in distribution facility

Price\*: 4619.00 USD



### Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip unit technology	Magnetic
Breaking capacity code	A
Accessory / separate part type	Handle

### Complementary

Line Rated Current	250 A
Poles description	3P
Breaking capacity	42 KA 120 V AC 42 KA 240 V AC 30 KA 480Y/277 V AC 30 KA 480 V AC 22 KA 600 V AC 10 KA 125 V DC 10 KA 250 V DC
[Ue] rated operational voltage	600 V AC
Mounting mode	Unit mount
Electrical connection	Lugs load Terminal line
AWG gauge	AWG 1...600 kcmil aluminium/copper)1 AWG 1...250 kcmil aluminium/copper)2
Terminal identifier	AL400LA
Magnetic hold current	1250 A
Magnetic tripping current	2500 A
Operator profile	Short lever
Wiring configuration	3-wire
Maximum Height	11 In (279.40 mm)
Width	6 In (152.40 mm)

Depth	5.84 In (148.34 mm)
Tightening torque	115.06 Lbf.In (13 N.m) 0.07...0.47 in <sup>2</sup> (42...304 mm <sup>2</sup> ) AWG 1...600 kcmil 115.06 Lbf.In (13 N.m) 0.07...0.20 in <sup>2</sup> (42...127 mm <sup>2</sup> ) AWG 1...250 kcmil)

## Environment

Product certifications	IEC UL Listed CSA
------------------------	-------------------------

## Ordering and shipping details

Category	00935 - LAL/LHL BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901530046
Nbr. of units in pkg.	1
Package weight(Lbs)	15.8 Lb(US) (7.17 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	8.90 In (22.606 cm)
Package 1 width	11.50 In (29.210 cm)
Package 1 Length	17.40 In (44.196 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DIDP and DIN-P which is known to the State of California to cause Carcinogen and Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**