

LAP36300MB

FA/LA MOLDED CASE CIRCUIT BREAKER, 600V, 300A, 3P, I-Line, SHORT HANDLE



by Schneider Electric

Product availability: Stock - Normally stocked in distribution facility

Price*: 4619.00 USD



Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip unit technology	Magnetic
Breaking capacity code	A
Accessory / separate part type	Handle

Complementary

Line Rated Current	300 A
Poles description	3P
Breaking capacity	42 KA 120 V AC 42 KA 240 V AC 30 KA 480Y/277 V AC 30 KA 480 V AC 22 KA 600 V AC 10 KA 250 V DC
[Ue] rated operational voltage	600 V AC
Mounting mode	Unit mount
Electrical connection	Lugs load Terminal line
AWG gauge	AWG 1...600 kcmil aluminium/copper)1 AWG 1...250 kcmil aluminium/copper)2
Terminal identifier	AL400LA
Magnetic hold current	1500 A
Magnetic tripping current	3000 A
Operator profile	Short lever
Wiring configuration	3-wire
Maximum Height	11 In (279.40 mm)
Width	6 In (152.40 mm)
Depth	5.84 In (148.34 mm)

Environment

Product certifications	IEC UL Listed CSA
------------------------	-------------------------

Ordering and shipping details

Category	00935 - LAL/LHL BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901530060
Package weight(Lbs)	15.8 Lb(US) (7.17 kg)
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DIDP and DIN-P which is known to the State of California to cause Carcinogen and Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**