



Main

Range of product	TeSys
Device short name	LC4
Product or component type	DOL starter
Motor power kW	11 kW at 380...400 V AC 50/60 Hz 11 kW at 415 V AC 50/60 Hz 11 kW at 440 V AC 50/60 Hz 15 kW at 500 V AC 50/60 Hz 5.5 kW at 220...230 V AC 50/60 Hz
Utilisation category	AC-3
[Ue] rated operational voltage	110 V AC 50/60 Hz
[Ie] rated operational current	<= 25 A

Complementary

Device composition	Contacteur Fuse disconnecter
Mounting support	Plate
Width	86 mm
Height	173 mm
Depth	98 mm
Product weight	1.58 kg

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0831 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.