

# Product data sheet

## Characteristics

# LH26150AC

## LH MOLDED CASE CIRCUIT BREAKER, 600V, 150A, 2P, 2PH



Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip unit technology	Thermal-magnetic
Breaking capacity code	H

### Complementary

Line Rated Current	150 A
Poles description	2P
Breaking capacity	65 kA at 240 V AC 35 kA at 480 V AC 25 kA at 600 V AC 50 kA at 250 V DC 35 kA at 480Y/277 V AC 20 kA at 500 V DC 25 kA at 600Y/347 V AC
System Voltage	250 V DC 500 V DC 600 V AC
Mounting mode	I-Line
Electrical connection	I-Line connection line Lugs load
AWG gauge	AWG 1...600 kcmil (aluminium/copper) 1 cable(s) AWG 1...250 kcmil (aluminium/copper) 2 cable(s)
Terminal identifier	AL400LA
Magnetic hold current	750 A
Magnetic tripping current	1500 A
Wiring configuration	2-wire
Phase connection	AC
Height	11 in
Width	6 in
Depth	5.84 in

### Environment

Product certifications	CSA UL listed
------------------------	------------------

### Ordering and shipping details

Category	01040 - LA/LH BRKR, SW, MAG-GARD
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	15.950000000000001
Returnability	Y
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

Product Life Status : **Commercialised**