

Product data sheet

Characteristics

LH26225AC

LH MOLDED CASE CIRCUIT BREAKER, 600V,
225A, 2P, 2PH



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip unit technology	Thermal-magnetic
Breaking capacity code	H

Complementary

Line Rated Current	225 A
Poles description	2P
Breaking capacity	65 kA at 240 V AC 35 kA at 480 V AC 25 kA at 600 V AC 50 kA at 250 V DC 35 kA at 480Y/277 V AC 20 kA at 500 V DC 25 kA at 600Y/347 V AC
System Voltage	250 V DC 500 V DC 600 V AC
Mounting mode	I-Line
Electrical connection	I-Line connection line Lugs load
AWG gauge	AWG 1...600 kcmil (aluminium/copper) 1 cable(s) AWG 1...250 kcmil (aluminium/copper) 2 cable(s)
Terminal identifier	AL400LA
Magnetic hold current	1125 A
Magnetic tripping current	2250 A
Wiring configuration	2-wire
Phase connection	AC
Height	11 in
Width	6 in
Depth	5.84 in

Environment

Product certifications	CSA UL listed
------------------------	------------------

Ordering and shipping details

Category	01040 - LA/LH BRKR, SW, MAG-GARD
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	16.23
Returnability	Y
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Product Life Status : **Commercialised**