



## Main

Product name	Glass Touch Panels
Product or component type	Door panel with configurable touchscreen
Device application	Hotel Bell switch Monitoring Signalling
Colour tint	Panelcolor option available in black Panelcolor option available in white Panelcolor option available in silver Panelcolor option available in champagne gold Buttoncolor option available in white Buttoncolor option available in amber Buttoncolor option available in blue Buttoncolor option available in light green Buttoncolor option available in red Buttoncolor option available in grey

## Complementary

Control button type	1 configurable bell touch buttons
Local signalling	3 configurable indicator light 1 indicator light presence indicator for
Marking	Room number
[Us] rated supply voltage	24 V DC
Current consumption	30 mA
Communication port protocol	Modbus serial over RS485
Mounting mode	Snap-in Magnetic
Height	Standard : 160 mm Optional : 160 mm
Width	Standard : 120 mm Optional : 120 mm
Depth	33 mm standard : 33 mm optional :
Relative humidity	10...95 % non-condensing when in operation
Order type	Mockup sample order

## Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C

Product Life Status : **Commercialised**