



Main

Product name	Glass Touch Panels
Product or component type	Keycard holder with configurable touchscreen panel
Device application	Ventilation Lighting Hotel Bell switch Monitoring Remote control Energy efficiency
Colour tint	Panelcolor option available in black Panelcolor option available in white Panelcolor option available in silver Panelcolor option available in champagne gold Buttoncolor option available in white Buttoncolor option available in amber Buttoncolor option available in blue Buttoncolor option available in light green Buttoncolor option available in red Buttoncolor option available in grey

Complementary

Control button type	3 configurable touch buttons
[Us] rated supply voltage	24 V DC
Current consumption	30 mA
Communication port protocol	Modbus serial over RS485
Mounting mode	Snap-in Magnetic
Height	Standard : 105 mm Optional : 95 mm
Width	Standard : 105 mm Optional : 95 mm
Depth	43 mm standard : 43 mm optional :
Relative humidity	10...95 % non-condensing when in operation
Order type	Product order

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C

Product Life Status : **Commercialised**