



Main

Range compatibility	PowerPact B
Product or component type	Cable connector
Device short name	Connectors
Accessory / separate part type	Connection accessories
Poles description	3P

Complementary

Quantity per set	Set of 1
Location of connection	Downstream Upstream
[In] rated current	15...125 A for copper 15...100 A for aluminium
Conductor material	Steel
Connections - terminals	Screw terminal - 1 cable(s) 2.5...95 mm ² (AWG 14...AWG 3/0) - solid Screw terminal 2.5...95 mm ² (AWG 14...AWG 3/0) - stranded Screw terminal 2.5...70 mm ² (AWG 6...AWG 2/0) - fine stranded
Current of common	10 A for 0.5...6 mm ² (AWG 20...AWG 10), stranded or fine stranded 10 A for 1.5...6 mm ² (AWG 20...AWG 10), rigid

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Product Life Status : **Commercialised**