



## Main

Range	Masterpact
Device short name	MCH
Product or component type	Motor mechanism
Device application	Control
Range compatibility	Masterpact MTZ2 Masterpact MTZ3

## Complementary

Control type	Standard
[Uc] control circuit voltage	380...415 V AC 50/60 Hz
Threshold tripping voltage	0.85...1.1 Un
Maximum power consumption in VA	180 VA
Overcurrent protection	2...3 x In 0.1 s
Maximum charging time	4 S
Maximum operating frequency	<= 3 cycles per minute
Rated voltage	Limit switch contact at 240 V 10 A

## Environment

Provided equipment	1 instruction sheet
Offer type	Spare part

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

Product Life Status : **Commercialised**