



Main

Range	Masterpact
Product or component type	Switch disconnecter
Device application	Distribution
Switch-disconnector name	Masterpact MTZ3 40 HA
Poles description	3P
Network type	AC
Network frequency	50/60 Hz

Complementary

Control type	Push-button
Mounting mode	Fixed
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-3
[Ie] rated operational current	4000 A AC 50/60 Hz 690 V
[Ui] rated insulation voltage	1000 V AC 50/60 Hz conforming to IEC 60947-3
[Uimp] rated impulse withstand voltage	12 KV conforming to IEC 60947-3
[Icw] rated short-time withstand current	85 KA during 1 s conforming to IEC 60947-3 85 KA during 3 s conforming to IEC 60947-3
[Icm] rated short-circuit making capacity	187 KA peak 220...690 V AC at 50/60 Hz
Utilisation category	AC-23A AC-3
Breaking capacity code	HA
Suitability for isolation	Yes conforming to IEC 60947-3
Contact position indicator	Yes
Visible break	No
Mechanical durability	10000 Cycles with maintenance conforming to IEC 60947-3
Electrical durability	AC-23A: 1500 cycles 440 V AC 50/60 Hz conforming to IEC 60947-3 AC-23A: 1500 cycles 690 V AC 50/60 Hz conforming to IEC 60947-3
Connection pitch	230 Mm
Height	Drawout switch disconnecter without chassis: 300 mm
Width	Drawout switch disconnecter without chassis: 378 mm
Depth	Drawout switch disconnecter without chassis: 300 mm

Environment

Net weight	120 Kg
Standards	EN/IEC 60947-3
Product certifications	IECEE CB Scheme
IP degree of protection	IP30
Pollution degree	3 conforming to IEC 60947-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**