



Main

Range	Masterpact
Product or component type	Ethernet interface module
Device application	Communication
Range compatibility	Masterpact MTZ2 circuit breaker Masterpact MTZ3 circuit breaker Masterpact MTZ1 circuit breaker
Commercial reference	LV851100SP LV851001SP LV851200SP
Device mounting	Embedded

Complementary

Communication gateway	Ethernet TCP/IP to Modbus
Communication network type	ULP, CANopen on USB Ethernet, Ethernet TCP/IP/10/100 Mbps on RJ45
Mounting mode	Drawout
Mounting support	DIN rail
Localisation on device	Chassis
Maximum supply current	3 A
Power consumption in W	72 W
Product certifications	FCC EAC CE
Standards	IACS E10 IEC 60947-6-2 IEC 60950
Height	51 Mm
Width	51 Mm
Depth	52.5 Mm
Net weight	0.075 Kg
Web server	Embedded

Environment

IP degree of protection	IP30
Ambient air temperature for operation	-20...70 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**