

Main

Range of product	PacDrive 3
Product or component type	SCARA robot
Device short name	STS40

Complementary

Number of axis	4
Operating position	Rotational 360°
Operating travel	0...800 mm horizontal 0...200 mm vertical
Repeat accuracy	+/- 0.01 mm
Permanent permissible load	17.64 lb(US) (8 kg)
Nominal speed	2000 mm/s axis 3 4.92 m/s axis 1 4.92 m/s axis 2
Maximum actuation speed	2220 mm/s axis 3 6.91 m/s axis 1 6.91 m/s axis 2
Angular speed	450°/S nominal axis 1 650°/S maximum axis 1 600°/S nominal axis 2 800°/S maximum axis 2 1200°/S nominal axis 4 1929°/S maximum axis 4
Product weight	110.23 lb(US) (50 kg)
Range compatibility	Lexium 62 motor

Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

Ordering and shipping details

Category	18357 - PACDRIVE ROBOTIC
Discount Schedule	PC52
GTIN	003606489593988
Nbr. of units in pkg.	1
Package weight(Lbs)	147.71000000000001
Returnability	N

Product Life Status : Commercialised