

Product data sheet

Characteristics

LXMSTS60F2A2000

STS60 - Floor - Ball screw 200 - ARMIO Board
with user I/O cable

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	PacDrive 3
Product or component type	SCARA robot
Device short name	STS60

Complementary

Number of axis	4
Operating position	Rotational 360°
Operating travel	0...200 mm vertical 0...1200 mm horizontal
Repeat accuracy	+/- 0.01 mm
Permanent permissible load	17.64 lb(US) (8 kg)
Nominal speed	2000 mm/s axis 3 6.39 m/s axis 1 6.39 m/s axis 2
Maximum actuation speed	2220 mm/s axis 3 8.01 m/s axis 1 8.01 m/s axis 2
Angular speed	1200°/S nominal axis 4 1929°/S maximum axis 4 385°/S nominal axis 1 490°/S maximum axis 1 500°/S nominal axis 2 610°/S maximum axis 2
Product weight	122.14 lb(US) (55.4 kg)
Range compatibility	Lexium 62 motor

Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

Ordering and shipping details

Category	18357 - PACDRIVE ROBOTIC
Discount Schedule	PC52
GTIN	003606489594121
Nbr. of units in pkg.	1
Package weight(Lbs)	158.72999999999999
Returnability	N

Product Life Status : Commercialised