



Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Basic
Number of gangs	2 gangs horizontal
Fixing mode	Clip-in
Cover frame colour tint	Ivory
Decoration colour	Ivory

Complementary

Material	ASA + PC: decorative frame ABS (acrylonitrile butadiene-styrene): cover frame
Standards	EN 60669-1
Height	80 Mm
Width	156 Mm
Depth	14 Mm
Distance between centers	71 Mm
Net weight	0.029 Kg

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Petrol Acetone Bleach Liquid soap Ammonia Alcohol Window-cleaning fluid Oil UV resistant
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**